

Project Name

Location

Prepared By



SATCO S26572

F30T12/D/RS

General

Status	Active
Watts	30
Shape	T12
Base	Medium Bi Pin
ANSI Base	G13
CCT (Kelvin)	6500
Temperature	Daylight
CRI	74
Lumens	1750
Beam Spread	360
Hours Rated	16000
Lamp Type	Linear
Technology	Fluorescent

Physical

MOL	35.22
MOD	1.50

Compliance

California Status	Lawful for sale in California
SDS Sheet	Linear_Fluorescent_Lamp

Notes

[www] 01-29-2021 11:42:02