Project Name

Location	Prepared By

SATCO S28930

40W/LED/WP/CCT/EX39/100-277V

Notes

[www] 01-17-2022 02:16:06

General

Status	Active
Watts	20W/30W/40W
HID Equivalent	175W
Volts	100V-277V
Shape	Corncob
Base	Mogul Extended
ANSI Base	EX39
Finish	White
CCT (Kelvin)	3000K/4000K/5000K
CRI	80
Lumens	3200L/4700L/6000L
Beam Spread	180
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Ballasting Requirements	Ballast Bypass

Electrical

Operating Frequency	50/60 Hz
Dimming Note	Dimmable only via the wattage/lumen selectable dial included on lamp
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)

Physical

MOL	8.43
MOD	3.62
Housing Color	White

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus Classified; cULus Listed
Location Rating	Damp
Energy Star	No
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

For More Information Visit:
http://www.satco.com/