

Project Name

Location

Prepared By



IMAGE NOT AVAILABLE

SATCO S29593

9.5A19/LED/827/ND/120V

Notes

[www] 02-09-2021 10:30:55

General

Status	Active
Watts	9.5
Incandescent Equivalent	60
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted
CCT (Kelvin)	2700
Temperature	Warm White
CRI	80
Lumens	800
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Power Factor	0.6
Operating Temperature	-25C (-13F) to a maximum of 45C (113F)

Physical

MOL	4.33
MOD	2.36
Housing Color	White
Weight (lb.)	0.095

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2370419
California Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp