

Project Name

Location

Prepared By



IMAGE NOT AVAILABLE

SATCO S29924

40T8/LED/96-840/BP/R17D

Notes

[www] 07-26-2021 03:24:29

General

Status	Active
Watts	40W
Volts	120V-277V
Ballast Type	Type B
Shape	T8
Base	Recessed Double Contact HO/VHO
ANSI Base	R17d
Nominal Length	96.00
Finish	White
CCT (Kelvin)	4000
Temperature	Cool White
CRI	82
Lumens	5500L
Beam Spread	210
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60 Hz

Physical

MOL	94.00
MOD	1.00

Additional Information

Additional Info	Suitable for Emergency Lighting only with Satco EM Driver #S8002
Shatter-Proof Type	PET Coated
Warranty	5 Year Limited - T8 LED Bulbs

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Lawful for sale in California
FCC Compliant	Yes
NSF Approved	Yes