

Project Name

Location

Prepared By



SATCO S39720

25T5/LED/46-865/BP/HO/SE-DE

Notes

[www] 07-11-2022 03:01:19

General

Status	Active
Watts	25W
Fluorescent Equivalent	54W
Volts	120V-277V
Ballast Type	Type B
Shape	T5
Base	Miniature Bi Pin
ANSI Base	G5
Nominal Length	48.00
Finish	Frost
CCT (Kelvin)	6500K
Temperature	Daylight
CRI	83
Lumens	3400L
Beam Spread	180
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Operating Frequency	50/60 Hz
Power Factor	0.9
THD	<25
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	46.00
MOD	0.83
Material	Aluminum
Lens Finish	Frost
Lens Material	Glass
Housing Color	Silver
Weight (lb.)	0.20

Additional Information

Tube Guard Use	Not Approved
Warranty	5 Year Limited - T5 LED Bulbs - Ballast Bypass

Compliance

Safety Listing	cULus - Classified; cULus - Certified
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PILKXR6N
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes

NSF Approved

Yes

SDS Sheet

LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

