Project Name

Location	Prepared By

SATCO S39750

30W/LED/HID/MB-G3/50K/100-277V

[www] 10-26-2020 00:08:10

Notes

General

Status	Active
Watts	30
Incandescent Equivalent	200
Fluorescent Equivalent	55
HID Equivalent	150
Volts	100V-277V
Shape	Corncob
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	4200
Beam Spread	120;150;260
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	LED HID
Technology	LED
Min Compartment Size	Width: 8.00 in. Depth: 8.00 in. Height: 11.00 in.

Electrical

Operating Frequency	50/60 Hz
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)

Physical

MOL	6.69
MOD	3.35
Housing Color	White
Photocell	Optional Add-On
Weight (lb.)	1.37

Additional Information

Additional Info	PIR Sensor available as an accessory
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Specification Note	Closed 260 deg; Partial 150 deg; Open 120 deg
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes

For More Information Visit:
https://www.satco.com/