

Project Name

Location

Prepared By



Notes

[www] 10-29-2020 00:05:10

General

Status	Active
Watts	40
Incandescent Equivalent	300
Fluorescent Equivalent	65
HID Equivalent	175
Volts	100V-277V
Shape	Comcob
Base	Mogul Extended
ANSI Base	EX39
Finish	Clear
CCT (Kelvin)	2700
Temperature	Warm White
CRI	80
Lumens	5120
Beam Spread	120;150;260
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	LED HID
Technology	LED
Min Compartment Size	Width: 8.00 in. Depth: 8.00 in. Height: 11.00 in.

Electrical

Operating Frequency	50/60 Hz
Power Factor	>0.9
Surge Protection	Built-in surge protection - 4KV
THD	<20%
Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)

Physical

MOL	7.24
MOD	3.35
Housing Color	White
Photocell	Optional Add-On
Weight (lb.)	1.85

Additional Information

Additional Info	PIR Sensor available as an accessory
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Specification Note	Closed 260 deg; Partial 150 deg; Open 120 deg
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No

DLC Approved	Yes
DLC ID	PLQ3VZ94GZN0
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	LED_Lamp

