

Project Name

Location

Prepared By



## SATCO S3990

9T8/LED/24-830/BP/SE-DE

### Notes

[www] 03-09-2021 01:43:27

### General

Status	Active
Watts	9
Volts	120-277V
Ballast Type	Type B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Finish	Gloss White
CCT (Kelvin)	3000
Temperature	Warm White
CRI	82
Lumens	1100
Beam Spread	210
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	T8
Technology	LED

### Electrical

Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60 Hz
Power Factor	0.9
THD	0.2
Operating Temperature	-20C (-4F) to a maximum of 45C (113F)

### Physical

MOL	24.00
MOD	1.1
Material	Glass
Lens Material	Glass
Housing Color	White
Weight (lb.)	0.24

### Additional Information

Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass
----------	--

### Compliance

Safety Listing	cULus Classified
Location Rating	Damp
DLC Approved	Yes
DLC ID	PLVVYBG8LEVK
California Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes

