


Dimensional Drawing for: S39904, S39905, S39906, S39907

8. DIMENSIONS



SYMBOL	MIN	TYP	MAX	UNIT
A	/	--	1199.4	mm
B	1204.0	--	1206.5	mm
C	1210.8	--	1213.6	mm
D	25.0	--	26.0	mm

9. Connection & Wiring

WIRING DIAGRAM

Single Ended



Double Ended

