

Project Name

Location

Prepared By



## SATCO S39905

17T8/LED/48-835/BP/SE-DE

### Notes

[www] 03-15-2021 00:27:52

### General

Status	Active
Watts	17
Volts	120-277V
Ballast Type	Type B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Finish	Gloss White
CCT (Kelvin)	3500
Temperature	Neutral White
CRI	82
Lumens	2100
Beam Spread	210
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	T8
Technology	LED

### Electrical

Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60 Hz
Power Factor	0.9
THD	0.2
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

### Physical

MOL	48.00
MOD	1.1
Material	Glass
Lens Material	Glass
Housing Color	White
Weight (lb.)	0.44

### Additional Information

Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass
----------	--

### Compliance

Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLPOXR8SWHON
California Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes

