



S7930

F14T8/CW

GENERAL SPECIFICATIONS

| | |
|--------------------|---------------|
| Shape: | T8 |
| Wattage: | 14W |
| Color Temperature: | 4100K |
| Length: | 14.22" |
| Base: | Medium Bi Pin |



TECHNICAL SPECIFICATIONS

| | | | |
|--------------------|---------------|---------------|-------------|
| Wattage: | 14W | Lumen Output: | 650L |
| Shape: | T8 | Technology: | Fluorescent |
| Base: | Medium Bi Pin | | |
| ANSI Base: | G13 | | |
| Finish: | Frost | | |
| Hours Rated: | 8000H | | |
| Color Temperature: | 4100K | | |
| CRI: | 62CRI | | |

DIMENSIONS

| | |
|---------|--------|
| MOL: | 14.22" |
| MOD: | 1.04" |
| Weight: | 0.0032 |

LISTINGS

| | |
|--------------|-------------------------|
| Energy Star: | No |
| Title 20: | Yes |
| CEC Terse: | Lawful for sale |
| SDS Class: | Linear_Fluorescent_Lamp |

PACKAGING

| | |
|------------------|----------------------|
| Each UPC: | 045923079306 |
| Each Quantity: | 1 |
| Each Dimensions: | 15.00 x 1.00 x 1.00" |

| | |
|------------------|----------------------|
| Case UPC: | 10045923079303 |
| Case Quantity: | 25 |
| Case Dimensions: | 15.75 x 5.91 x 6.06" |

110 Heartland Blvd.
 Brentwood, NY 11717
 PH 631-243-2022
 FX 631-243-2027

Distribution Centers
 New York, Florida,
 Texas, Washington,
 California, Puerto Rico

National Toll-Free
 800-43-SATCO
 (800-437-2826)
 www.satco.com

Copyright 2021
 Satco Products, Inc.
 All Rights Reserved
 June 7, 2021