

Project Name

Location

Prepared By



SATCO S8027

1W/LED/S14/CL/822/120V/ND/4PK

Notes

[www] 11-20-2023 01:02:49

General

Status	Active
Watts	1W
Incandescent Equivalent	11W
Volts	120V
Shape	S14
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2200K
Temperature	Warm White
CRI	80
Lumens	100L
Beam Spread	320
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	String Light
Technology	LED

Smart Product Info

IOT Enabled	No
-------------	----

Electrical

Operating Frequency	60Hz
Power Factor	0.5
Operating Position	Universal
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	3.43
MOD	1.18
Weight (lb.)	0.1

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	Exempt
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
IP Rating	IP20
RoHS Compliant	Yes
SDS Sheet	LED_Lamp