

NUVO TH488

12W LED FORGED TRACK HEAD

Notes			
	M	α	00
		w	(-1

aaaaal 10.05.2020 02:08:57

General	
Status	Active
Туре	Track Head
Wattage	12
Finish	Black
Beam Angle	24
CCT (Kelvin)	3000
Temperature	Warm White
Indoor or Outdoor Fixture	Indoor

Specifications	
CRI	90
Lumen Output	1020
Rated Hours	30000
Voltage	120V
Dimmable	Yes - Dimmable
Compatible Dimmers	Triac
Weight (lb.)	0.64

Dimensions	
Height (in.)	6.00
Width (in.)	2.75
Length (in.)	3.75

Compliance	
Safety Listing	cETLus
Location Rating	Dry
UL Application	Ceiling
Energy Star	No
CEC Status	Lawful for sale in California
CA Prop 65	Lead
RoHS Compliant	Yes

Λ	d	Ш	•		4	•	п	

Warranty 3 Year Limited - Fixtures







