SATCO' NUVO

Project Name

Location

Prepared By



NUVO TH499

12W LED PISTON TRACK HEAD

Notes

General Status Active Туре Track Head 12 Wattage Finish **Brushed Nickel Beam Angle** 36 CCT (Kelvin) 3000 Temperature Warm White Indoor or Outdoor Fixture Indoor Specifications CRI 90 Lumen Output 1020 Rated Hours 30000 Voltage 120V Dimmable Yes - Dimmable **Compatible Dimmers** Triac Weight (lb.) 0.77 Dimensions Height (in.) 5.25 Width (in.) 3.00 Length (in.) 4.00 Compliance Safety Listing cETLus Location Rating Dry **UL** Application Ceiling Energy Star No Lawful for sale in California CEC Status CA Prop 65 Lead **RoHS** Compliant Yes Additional Information

Warranty

3 Year Limited - Fixtures

For More Information Visit: <u>https://www.satco.com/</u>

