SATCO' NUVO

Project Name

Location

Prepared By



NUVO TH647

12W LED TRACK SM CYLINDER 36

Notes

General Status Active Track Head Туре 12W Wattage Finish Matte Black / Brushed Brass Beam Angle 36 CCT (Kelvin) 3000K Warm White Temperature Base Integrated ANSI Base Integrated Indoor or Outdoor Fixture Indoor Specifications CRI 90 Lumen Output 1020L Rated Hours 30000 120V Voltage Dimmable Yes-Dimmable **Dimming Note** 120V Only Weight (lb.) 0.44 Dimensions Height (in.) 2.25 Width (in.) 2.25 Length (in.) 3.375 Extension (in.) 5.375 Compliance Safety Listing cETLus - Listed Location Rating Dry **UL** Application Track California T24 2016 - 2022 JA8 CA T20 / T24 Rationale Listed California Status Lawful for sale in California Title 20 / 24 Status California T24 Listed California Prop 65 Lead Additional Information

Warranty

3 Year Limited - Fixtures

For More Information Visit: <u>https://www.satco.com/</u>

