



Great value unit – high volume sealing

- Ideal for high volume sealing
- Plug-in electronic timer for variable control
- All metal construction
- Heavy duty
- No warm-up time
- Sits on rectangular base for stability

More Details:

FS-Series Foot Sealers are ideal for high-volume poly bag sealing and other thermoplastic sealing. Available in 14", 18", and 26" lengths with an 8mm seal width, the FS-Series foot sealers are capable of sealing 15-20 bags/minute. Depending on the model of the sealer, materials up to 26" wide and a total thickness of 20mil can be sealed. These sealers allow you to keep your hands free for quicker and more accurate sealing. The machines are also equipped with a plug-in timer. Once the timer is set, the sealer provides a consistently flat seal.

FS-Series Sealers are light blue in color. Depending on the model of the sealer, materials up to 24" wide with a 16 mil total thickness can be sealed. The sealers include a 26" pedestal, a 2" base, adjustable work table, and adjustable foot control. The manufacturer's replacement kit includes two elements, a sheet of PTFE cover and tools. Elements are easily replaceable due to the clip type element holder.

Easy to Operate: Set the timer. Insert the bag between the two sealing bars and press down on the foot board. Hold down the foot board for an additional 2-3 seconds after the timer light goes off to set the seal.

Features:

	FS-358F	FS-458F	FS-658F
Power Supply	110V / 50Hz	110V / 50Hz	110V / 50Hz
Watts	600W	800W	1000W
Seal Length	14"	18"	26"
Seal Width	8mm	8mm	8mm
Weight	63-lbs	65-lbs	68-lbs
Dimensions (L x W x H)	16" x 20" x 34"	20" x 20" x 34"	28" x 20" x 34"