

- Ideal for high volume sealing
- Plug-in electronic timer for variable control
- All metal construction
- Heavy duty
- No warm-up time
- Sits on rectangular base for stability

TISF Foot Sealers are ideal for high-volume poly bag sealing. Available in 12", 18", and 24" lengths with a 2.7mm or 5mm seal, the TISF-Series foot sealers are capable of sealing 15-20 bags/minute. These sealers allow you to keep your hands free for quicker and more accurate sealing. The machines are also equipped with a plug-in timer. Once the timer is set, the sealer provides a consistently flat seal.

TISF Sealers are light blue in color. Depending on the model of the sealer, materials up to 24" wide with a 20 mil total thickness can be sealed. Distance from floor to sealing area is 30". The sealers include a 26" pedestal, a 2" base, adjustable work table, and adjustable foot control. Work table measures 12" x 5" while the adjusting plate measures 9 1/2" x 10". An optional 36" pedestal for standing operation is available. The manufacturer's replacement kit includes two elements.

Easy to Operate: Set the timer. Insert the bag between the two sealing bars and press down on the foot board. Hold down the foot board for an additional 2-3 seconds after the timer light goes off to set the seal.



Model #	Seal Length	Seal Width	Watts	Weight (lbs)
TISF-302	12"	2MM	400W	44 / 9
TISF-305	12"	5MM	600W	47 / 9
TISF-452	18"	2MM	600W	49 / 9
TISF-455	18"	5MM	900W	49 / 9
TISF-602	24"	2MM	800W	59 / 9
TISF-605	24"	5MM	1200W	59 / 9

Sealer ships as two packages

RS-8

A 3-line mountable imprinter is an available option. The imprinter mounts on the upper jaw of the sealer. Seal and print in one single operation.

Ribbon colors available: black, red, & white

MFG 02.12.09.
EXP 00.12.09.
LOT 735 B Q D

