



Easy to operate

- Ideal for high volume sealing
- Plug-in electronic timer for variable control
- All metal construction
- No warm-up time
- Sits on rectangular base for stability
- ETL Listed (2.5mm seal width units)

More Details:

KF-Series Foot Sealers are ideal for high volume poly bag and other thermoplastic sealing. The sealers are capable of sealing 15-20 bags per minute. These sealers allow you to keep both hands free for quicker and more accurate sealing. The machines are also equipped with a plug-in timer. The timer controls the sealing time needed for different materials. Once the timer is set, it will give a consistently flat seal. When seal is done, the signal light on the timer will turn off.

Our KF-Series foot sealers are available in 12", 18", and 24" with a 2.5mm or 5mm seal width. Depending on the model of the sealer, materials up to 24" wide and 16 mil total thickness can be sealed. The sealers include a 26" pedestal, a 2" base, an adjustable worktable and an adjustable foot control. Work table measures 12" x 6-1/2" and can adjust from 3-1/2" – 9" from the sealing base. The manufacturer's replacement kit includes two elements and one fuse. The 2mm seal width units are ETL Listed.

Easy to Operate: Set the timer. Insert the bag between the two sealing bars and press down on the foot board. Hold down the foot board for an additional 2-3 seconds after the timer light goes off to set the seal.

Specifications:

	Seal Length	Seal Width	Watts	Dimensions	Weight
KF-300F*	12"	2.5mm	400	15" x 14" x 35"	45
KF-305F	12"	5mm	600	15" x 14" x 35"	46
KF-450F*	18"	2.5mm	600	21" x 15" x 35"	47
KF-455F	18"	5mm	900	21" x 15" x 35"	48
KF-600F*	24"	2.5mm	800	28" x 16" x 35"	50
KF-605F	24"	5mm	1200	28" x 16" x 35"	51

* ETL Listed

