## SLV-3470

# **SPEAKMAN**<sup>®</sup>

## Sentinel Mark II® Diverter Trim, Shower and Tub Package (Valve not included)

### MODELS:

- SLV-3470: Includes VS-100 2.5 GPM (9.5 L/min) Flow Rate Hand Held Shower and S-2272-E2 2.0 GPM (7.6 L/min) Shower Head
- SLV-3470-E175: Includes VS-100-E175 1.75 GPM (6.6 L/min) Flow Rate Hand Held Shower and S-2272-E175 1.75 GPM (6.6 L/min) Shower Head

### **FEATURES**:

- CPT-3401: Diverter Shower Valve Trim
- S-2272-E2 or Shower Head S-2272-E175:
- S-2500: Shower Arm and Flange
- VS-100-PC or Hand Held Shower with VS-100-E175: Pause/Trickle Button
- VS-115: Supply Ell with Wall Flange
- VS-117: Vacuum Breaker
- S-1554: Tub Spout
- CPT-1110: Transfer Valve Trim (Valve not included)
- VS-145: 69 in. Metal Stainless Steel Hose

## VALVE OPTIONS:

• CPV-PB-DV:	Pressure Balance Diverter Valve Sweat & Thread Connections
• CPV-PB-DV-PXC:	Pressure Balance Diverter Valve PEX F1807 Crimp Inlet Connections
• CPV-PB-DV-PXE:	Pressure Balance Diverter Valve PEX F1960 Cold-Expansion Inlet Connections
• CPV-T2-DV:	Thermostatic Diverter Valve Sweat & Thread Connections
• CPV-T2-DV-PXC:	Thermostatic Diverter Valve PEX F1807 Crimp Inlet Connections
• CPV-T2-DV-PXE:	Thermostatic Diverter Valve PEX F1960 Cold-Expansion Inlet Connections
• CPV-TV:	Two-Way Diverter Valve for use with CPT-1110

#### Information continues on next page

## STOCK FINISHES:



### STANDARDS:

- ASME A112.18.1/CSA B125.1 certified
- ADA Complaint

#### WARRANTY:

Visit www.speakman.com for full product warranty information

See Speakman.com For Warranty Information

Architect/Engineer Approval Space:




P: 800-537-2107 F: 800-977-2747 W: WWW.SPEAKMAN.COM R: 04-FEBRUARY 2022

## SLV-3470

## **SPEAKMAN**®

Sentinel Mark II® Diverter Trim, Shower and Tub Package (Valve not included)



DIMENSION	CPV-PB-DV	CPV-T2	CPV-PB-DV-PXC	CPV-PB-DV-PXE	CPV-T2-PXC	CPV-T2-PXE
Α	7/16" (11mm)	9/16" (14mm)	7/16" (11mm)		9/16" (14mm)	
В	4-15/16" (125mm)	5-1/16" (128mm)	4-15/16" (125mm)		5-1/16" (128mm)	
С	4-13/16" (123mm)	5-7/8" (150mm)	4-13/16" (123mm)		5-7/8" (150mm)	
D	2-1/2" (63mm) MIN TO 3-1/2" (89mm) MAX					
E			3-1/8" (79mm) MIN TC	4-1/8" (105mm) MAX	3-3/16" (81mm) MIN TO 4	-3/16" (106mm) MAX

Architect/Engineer Approval Space:

R: 04-FEBRUARY 2022

P: 800-537-2107

F: 800-977-2747

W: WWW.SPEAKMAN.COM