

Stainless Steel Faucet Connector

MODELS:

Catalog #	Description	A
SPK-57576US	1/2" FIP x 1/2" FIP	12"
SPK-57577US	1/2" FIP x 1/2" FIP	16"
SPK-57578US	1/2" FIP x 1/2" FIP	20"
SPK-57672US	1/2" OD x 1/2" FIP	12"
SPK-57673US	1/2" OD x 1/2" FIP	16"
SPK-57674US	1/2" OD x 1/2" FIP	20"
SPK-57634US	3/8" OD x 1/2" FIP	6"
SPK-57635US	3/8" OD x 1/2" FIP	9"
SPK-57572US	3/8" OD x 1/2" FIP	12"
SPK-57573US	3/8" OD x 1/2" FIP	16"
SPK-57574US	3/8" OD x 1/2" FIP	20"
SPK-57575US	3/8" OD x 1/2" FIP	24"
SPK-57633US	3/8" OD x 1/2" FIP	30"
SPK-57660US	3/8" OD x 1/2" FIP	36"
SPK-57661US	3/8" OD x 3/8" Com	12"
SPK-57662US	3/8" OD x 3/8" Com	20"



CONSTRUCTION:

- Corrosion Resistant 304 Stainless Steel Braiding.
- Reinforced 2 Ply PVC Inner Lining.
- Superior Strength and Flexibility.
- 360° Circular Triple Crimp.
- Longer Barb and Plated Brass Sleeve.
- Two Nickel Plated Brass Nuts.
- EPDM Cone Washer attached to each end of the hose for sealing

OPERATION:

- Burst Tested to Exceed 2500 PSI.


STANDARDS:

- ASME A112.18.6/CSA B125.6 certified
- NSF/ANSI 372 certified

WARRANTY:

Visit www.speakman.com for full product warranty information

- 5 Year Limited Warranty



1. All dimensions are in inches (millimeters) unless otherwise specified and are subject to change without notice.

Architect/Engineer Approval Space:

P: 800-537-2107
 F: 800-977-2747
 W: WWW.SPEAKMAN.COM
 R: 01-JULY 2021