VSR-235000

Exhilaration Shower Combination

MODEL:

- VSR-235000-E2: 2.0 GPM (7.6 L/min) flow rate
- VSR-235000-E175: 1.75 GPM (6.6 L/min) flow rate

FEATURES:

- 3-way diverter, both showers can be used at the same time
- VSR-5000 Exhilaration hand shower
- SR-5000 Exhilaration shower head
- Combined 688 spray outlets, 25 spray pattern combinations including pause mode
- Exhilaration Spray Technology® includes patented Speakman Reaction high performance turbine engine
- 5 setting spray face includes Inner Massage, Satin Spray, Speakman Reaction, Rain, and Pause
- Spray adjusting faceplate, with optimum spray setting when in vertical position
- Plastic body construction
- 1/2" -14 NPS male inlet
- 5' metal hose with (1) 1/2" -14 NPS female inlet and (1) 1/2"-14 NPS female outlet
- Customer will need to install a backflow prevention device for plumbing code compliance

STOCK FINISH:



SPECIALTY FINISH:



STANDARDS:

- ASME A112.18.1/CSA B125.1 certified
- WaterSense certified
- CEC (CA Energy Commission) certified, 1.75, 1.5 GPM only
- ADA Compliant

WARRANTY:

- Visit www.speakman.com for full product warranty information
- Limited Lifetime Warranty (residential)
- 1 Year Limited Warranty (commercial)

 $7\frac{1}{16}$ [190mm] $15\frac{7}{8}$ [403mm] 1/2"-14 NPT THREADED 1/2"-14 NPSM FEMALE INLET [1550mm] $7\frac{15}{16}$ " $7\overline{8}$ Î [202mm] [181mm] 13′8 İ [352mm]

WILL VARY BASED UPON YOUR INSTALLATION

1/2"-14 NPSM FEMALE

All dimensions are in inches (millimeters) unless otherwise specified and are subject to change without notice

Architect/Engineer Approval Space

Ρ:	800-537-2107
F:	800-977-2747

W: WWW.SPEAKMAN.COM

R: 02-APRIL 2022

SPEAKMAN[®]