

LS-FLOAT SWITCH SPECIFICATIONS

Level Sense Float Switch connects to a control device accepting an analog or digital input.

- Housing: Polypropylene, white
- Working Voltage: 5Vdc-12Vdc
- Max. Voltage: 24Vdc
- Max Wattage: 10W
- Max. Working Current: 0.5 Amp, 1.0 Amp Max
- Contact Resistance 0.2Ω
- Temperature: -4°F +176°F / (-20°C +80°C)
- 20 Feet of Cable
- Red wire to Positive, white wire to Negative (ground)
- Perfect for Arduio, Rasberry Pi, and home electronics projects.

LIMITED 2-YEAR WARRANTY

Sump Alarm, Inc. warrants to the original consumer that this product shall be free of manufacturing defects for five years after the date of consumer purchase. During that time period and subject to the conditions set forth below, Sump Alarm, Inc. will repair or replace, for the original consumer, any component which proves to be defective due to the materials or workmanship of Sump Alarm, Inc. This warranty does not apply: (a) to damage due to lightning or conditions beyond the control of Sump Alarm, Inc. (b) to defects or malfunctions resulting from failure to properly install, operate, or maintain the unit according with the instructions provided; (c) to failures resulting from the abuse, misuse, accident or negligence; (d) to units which are not installed in accordance with applicable local codes, ordinances or accepted trade practices, and (e) to units repaired and/or modified without the authorization of Sump Alarm, Inc. To obtain warranty service: The consumer shall assume all responsibility and expense for removal reinstallation and freight. ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS ARE LIMITED TO THE DURATION OF THIS WRITTEN WARRANTY. SUMP ALARM, INC. SHALL NOT, IN ANY MANNER, BE LIABLE FOR ANY INCIDENTAL OR CONSEQUENTIAL DAMAGES AS A RESULT OF A BREACH OF THIS WRITTEN WARRANTY OR ANY IMPLIED WARRANTY.

For help or assistance, call our support line at 314-787-8059 ext 2.