



The C2G Select Standard Speed HDMI with Ethernet Cable is perfect for home theater, desktop and commercial audio video applications requiring standard speed HDMI features and video resolutions up to 1080i. The CL2 rated cable jacket is designed to meet the requirements for in-wall installations. The Ethernet capabilities of the cable allow a user to connect multiple Ethernet enabled HDMI devices through a single Ethernet connection. This fully-functional, digital video and audio cable is tested to perform at industry standards and is backed by a lifetime warranty.

Features & Benefits

In-wall, CL2-rated jacket	Standard Speed HDMI Cable
Supports up to a 1080i video resolution	Gold plated connectors

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120425274	Country Of Origin	Vietnam
Application Sector	Residential, Commercial	Type	Cable

Dimensions

Cable Length	49 ft
--------------	-------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	23 AWG
Video Resolution	1080p	Bend Radius	70 mm
Cable Type	Standard Speed HDMI, Video	Jacket Rating	CL2 Rated, FT4 Rated
Data Transfer Rate	18 Gbps	Adapter Rear	HDMI Male
Adapter Front	HDMI Male		