



C2G
100ft (30.5m) Velocity™ RCA Stereo Audio Cable
Part No. CG-29103



Don't let your interconnects be the weak link in your audio system chain! This audio cable offers excellent sound quality because its bonded construction design delivers a neat, easy connection of audio signals. Twisted pair oxygen-free copper wire and foamed PE dielectric are optimized for audio signal transmission. The 100% foil shield protects the audio signals from electromagnetic interference (EMI) and radio frequency interference (RFI). Color-coded molded connectors and an ultra-flexible jacket enable easy installation. 24K gold-plated heavy duty contacts ensure a lifetime of performance.

Features & Benefits

Color coded, fully molded connectors
24K gold plated contacts

Ultra flexible PVC jacket
Tinned Oxygen Free Copper

Specifications

General Info

Product Line	C2G	Color	Blue
UPC Number	757120291039	Country Of Origin	Vietnam
Application Sector	Residential, Commercial	Type	Cable

Dimensions

Cable Length	100 ft
--------------	--------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Cable Type	Audio
Jacket Rating	Standard / Non-Rated	Adapter Rear	RCA Stereo Audio Male

Adapter Front

RCA Stereo Audio Male
