



The C2G Select VGA Video Extension Cable is perfect for extending VGA cable connectivity for in-home desktop or in-wall commercial applications which require video resolutions of up to QXGA (2048x1536). The CMG rated jacket provides a solution for in-wall applications, while the low-profile, rounded connectors make installing in tight spaces easy. This cable is designed to support high resolution video applications over long distances of up to 100ft. All 15 pins are wired providing support for DDC2 (E-DDC) and Extended Display Identification Data (EDID) signals, i.e. communication of the display's capabilities, ensuring that the content from the source is sent at the optimal resolution for the display.

<

Features & Benefits

In-wall, CMG-rated jacket

Supports up to a 2048x1536 resolution

All 15 pins wired to support DDC2 (E-DDC) and EDID

Low profile connectors

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120502425	Country Of Origin	China
Application Sector	Residential, Commercial	Type	Cable

Dimensions

Cable Length	50 ft
--------------	-------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	30 AWG
Video Resolution	QXGA (2048x1536)	Bend Radius	85 mm

Cable Type	Video, Extension	Jacket Rating	CMG Rated, FT4 Rated
Adapter Rear	VGA Female	Adapter Front	VGA Male
Voltage	30 V		
