



ArtiDiag500 & ArtiDiag600

Take Out The Guesswork

The ArtiDiag 500 and ArtiDiag 600 are mid-level scanners that provide the most essential information on US, Euro, and Asian cars. They perform diagnostics of the Engine, Transmission, ABS, and SRS Systems through a user-friendly interface. The vehicle history function eliminates the guesswork by recovering previous settings to fix computer tech issues faster and easier. Best of all, its AutoVIN feature allows for fast vehicle identification and battery voltage displays to diagnose even faster.

ArtiDiag 500 Features

- Diagnose 4 Main Systems (Engine, Transmission, ABS, and SRS) of 42 Brands
- Access to ECU Information
- Reads/Clears DTCs, Reads Vehicle Information, Views Freeze Frame Data, and More
- Displays, Graphs, and Merges Live Data Stream
- Includes AutoVIN Technology
- Provides the Vehicle's History Function
- Automatically Generates Diagnostic Reports
- Displays the Car's Battery Voltage in Real-Time
- DTC Look-up Library
- Online Feedback

ArtiDiag 600 Features

All of the ArtiDiag 500 Functions, Plus:

5 Maintenance Services: Brake, Oil, SAS, and TPMS Resets, as well as Throttle Relearn

What's in the Box

ArtiDiag500 / ArtiDiag600
Diagnostic Cable
Charging Cable
Quick-Start Guide
User's Manual
Carrying Bag

Comparison Chart

ArtiDiag500

- 5" LCD Screen
- 4 Systems Diagnostics for 42 Vehicle Makes

ArtiDiag600

- 5" LCD Screen
- 4 Systems Diagnostics for 42 Vehicle Makes
- 5 Maintenance Service Functions

ArtiDiag 800

- 7" LCD Screen
- 1.5 GHz Quad-Core Processor
- Full system diagnostics for 72 Makes
- 15 Maintenance Service Functions

ArtiDiag 800 BT

- 6" LCD Screen
- 1.8 GHz Quad-Core Processor
- Full system diagnostics for 96 Makes
- 28 Maintenance Service Functions
- Bluetooth VCI Communications

Specs

- Display: LCD 5-Inch, 1280*720 dpi
- Operating system: Android 7.1
- Operating voltage: 9~18V
- Storage Temperature: -4°F~158°F
- Working Temperature: 14°F~122°F
- Dimension: 232*126*34 mm (9.1*5.0*1.3 inch)
- Package size: 10.70*8.58*3.15 inches
- Length: 46.65 inches
- Net Weight: 1.2 lbs
- Multilingual Support: English, French, German, Spanish, Portuguese, Russian, Japanese, and Italian