



ArtiLink500

Practical Diagnostics

The ArtiLink 500 is a diagnostic scan tool that supports all 10 OBDII modes for most 1996 and newer vehicles. This device offers a one-click "Readiness Test Status" for smog test and quickly retrieves VIN, CIN, and CVN information. With the ArtiLink500 you get powerful functions at an affordable price point.

Features

- 3 LED DTC Indicators For an Easy Analysis of the Vehicle Status
- VCI Dongle with LED Flashlight for Easy Connection During Night Repairs
- Supports Full Modes of OBDII Diagnostics for most 1996 and newer vehicles
- Reads and Clears Codes
- Supports CAN, ISO9141, KWP2000, J1850 PWM, and J1850 VPW Protocols
- Turns off the Check Engine Light and Retrieves I/M Readiness Status for an Easy Smog Test
- Retrieves Freeze Frame Data, VIN, CIN, and VCN Information
- Includes a DTC Lookup Library for Detailed Information
- Multilingual Menu

Specs

- Display: LCD 2.8-Inch, 320X240
- Operating voltage: 9~18V
- Storage Temperature: -4°F~158°F
- Working Temperature: 14°F~122°F
- Dimension: 6.44*3.71*1.23 inches
- Length: 56.49 inches
- Net Weight: 9.52 oz

What's in the Box

- 1 ArtiLink 500 Code Reader
- 1 Quick Start Guide
- 1 User Manual
- 1 USB Cable

Comparison Chart

AL200	AL300	AL400	AL500	AL600
Features				
<ul style="list-style-type: none"> • Reads & Clears DTCs • Viewing Freeze Frame Data • Retrieving I/M Readiness Status • Viewing Vehicle Information 	All ArtiLink 200 Features plus: <ul style="list-style-type: none"> • O2 Sensor Test • On-board Monitor Test • DTC Lookup • EVAP Test • Multilingual Menu (7): English, French, Japanese, German, Portuguese, Russian, Spanish. 	All ArtiLink 200 Features plus: <ul style="list-style-type: none"> • O2 Sensor Test • On-board Monitor Test • DTC Lookup • Graph Live Data • OBDII Connector LED Light • Free Software Updates • EVAP Test 	All ArtiLink 200 Features plus: <ul style="list-style-type: none"> • O2 Sensor Test • On-board Monitor Test • DTC Lookup • Graph Live Data • OBDII Connector LED Light • Free Software Updates • EVAP Test • Print Via PC • Multilingual Menu (7): English, French, German, Spanish, Portuguese, Russian, Japanese 	All ArtiLink 200 Features plus: <ul style="list-style-type: none"> • O2 Sensor Test • On-board Monitor Test • DTC Lookup • Graph Live Data • OBDII Connector LED Light • Free Software Updates • EVAP Test • Print Via PC • Multilingual Menu (8): English, French, German, Spanish, Portuguese, Russian, Italian, Japanese
Specs				
<ul style="list-style-type: none"> • Display: 128x64 pixel display • Operating Voltage: 9~16V • Weight: 0.5 lbs 	<ul style="list-style-type: none"> • Display: 1.77 in Color Display • Operating Voltage: 9~18V • Weight: 0.5 lbs • Storage Temperature: -4°F ~158°F • Operating Temperature: 32°F ~122°F • Dimensions: 4.68 * 2.82 * 0.91 inches 	<ul style="list-style-type: none"> • Display: 2.4" Color • Operating Voltage: 9V~18V DC • Weight: 0.5 lbs • Storage Temperature: -4°F 158°F • Operating Temperature: 14°F ~122°F • Product Dimensions: 5.67*2.95*0.96 inches 	<ul style="list-style-type: none"> • Display: LCD 2.8-Inch, 320*240 pixels • Operating voltage: 9~18V • Weight: 0.6 lbs • Storage Temperature: 4°F ~158°F • Operating Temperature: 14°F ~122°F • Dimension: 6.44*3.71*1.23 inches 	<ul style="list-style-type: none"> • Display: 3.5-Inch LCD; 320*480 pixels • Operating Voltage: 9~18V • Weight: 1.1 lbs • Storage Temperature: -4°F ~158°F • Operating Temperature: 14°F ~122°F • Unit Dimension: 8.46*4.49*1.36 inches

CONTACT US     @topdonofficial

TOPDON TECHNOLOGY Co., Ltd. | WWW.TOPDON.COM

sales@topdon.com | +86-755-21612590 +1-833-629-4832 (North America)

Unit 2005 20/F, No.3040 Xinghai Avenue, Qianhai Shima Tower, Qianhai Shenzhen-Hong Kong Cooperation Zone, Shenzhen, P.R.China | 518000