

“UK” BS6312 OR BT631A MODULAR ADAPTER PA1921

TESTING | TROUBLESHOOTING | ACCURACY

Product Features:

- Nylon-reinforced ABS plastic body
- Easy-to-read wire layout
- Removable/replaceable patch cord
- Inline adapters
- Belt clip
- Notched copper contacts keep alligator clips attached during testing
- With “UK” BS6312 BT631A telephone plug cord as used in UK, Botswana, Cyprus, Eswatini, Gibraltar, Israel, Malta, New Zealand, Oman, Saudi Arabia, UAE, Zimbabwe etc



Packed: 95 x 65 x 40 mm, 3 3/4 x 2 5/8 x 1 5/8"

Weight: 62 g (2.2 oz)

1390 Aspen Way Vista, CA • 92081 TC-PA1921 05/20

Latin America Phone : 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927050
©2020 Tempo Communications Inc. • An ISO 9001 Company

EMEA Address: Tempo Communications Limited • Brecon House
William Brown Close • Cwmbran • NP44 3AB • UK • emeasales@tempocom.com

TempoCom.com | tel 800.642.2155 | sales@tempocom.com

 **TEMPO**[®]
COMMUNICATIONS

Renewed Vision. Innovation Forward.



Follow us @TempoComms