ULTIMATE TECHNICIAN KIT



PA4932



PA4923 Case, Tools Totem

- Main compartment features removable inner tote and 3 additional pockets
- Piano® divided tackle box neatly stores dies, blades & connectors
- Removable inner tote with 8 adjustable storage slots keeps smaller tools handy
- Detachable shoulder strap with 3 anchor points to carry bag horizontally or vertically
- Deep Velcro pockets holds large tools or test equipment
- Sturdy bottom prevents bag from flopping over when sitting upright

PA1561 Crimper, Snagless, All-in-One (Bulk)

- Also crimps RJ11/22 and RJ22 WE/SS style plugs
- Cuts and strips round or flat cable
- All metal construction
- Cushion grips for improved comfort and control
- For standard and "snagless" RJ45 connectors

NC-100 Tester, VDV NETcat (POP)

The NETcat® Micro Wiring tester is a device that verifies twisted pair and coaxial cables. It uses high-speed digital technology to check wiring continuity and correct allocation of wire pairs. NETcat Micro, NC-100 Tests shielded twisted pair (STP), unshielded twisted pair (UTP), and coaxial cables.

PA1116 Stripper UTP STP Flat Cable

- Cuts and strips multiple cable types: 4-, 6- and 8-conductor flat satin cables., 4-, 6- and 8-conductor UTP/STP data cables., 25-pair UTP/ STPdata and telephone cables
- Multi-conductor round bundled cables with a maximum diameter of .5 IN
- 14-8 AWG (2.5-75mm2) wire
- Nylon reinforced ABS plastic with stainless steel blade
- Fully adjustable with simple thumb screw
- Self-regulating to prevent nicking
- · Contoured finger grips for power cutting
- · Lanyard holes for wrist straps or key chains
- Small and compact, slips right into a pocket
- · Works left or right handed

PA1559 Crimper, MiniCoax Pro Unv, Bulk

- Crimps weatherproof linear CATV "F", BNC, RCA & right- angle compression-type connectors from all manufacturers
- Works with RG6, RG6 Quad, RG59 & RG62∆U coax cables
- Versatile tool accommodates multiple connectors
- The only tool with a single, reversible head eliminating need for adapters
- No additional parts, attachments or other tools required to change from one crimp style to another
- · Quickly & easily adjust crimp height
- Once properly set, lock with adjustment lock

601K-G Basic Tone & Probe Kit

The TEMPO Communications 601K-G tone and probe tracing kit allows technicians to identify wires from a bundle, to monitor voltage passing through the circuit, to check breaks in the circuit and to trace wires through walls. The TEMPO Tracing Kit includes the generator tone which injects a signal onto the cable to be traced and the tracing probe which is used to trace out the wire. Quick, Reliable, Connections.

PA1900 Wrench Can Drop-forged w/ Plastic Handle

- Strips outer jacket of AWG22/4 and 24/4 telephone cable
- Strips insulation of AWG 22 (.34 mm2) and AWG 24 (.20 mm2) wire
- 3/8 IN (9.5 mm) and 7/16 IN (11 mm) hex sockets for accessing panels
- Strips PVC insulation
- Durable shock-resistant design• For standard and "snagless" RJ45 connectors

PA1179 Cutter Dual Contour Cable

- Ideal for UTP and Coax, RG58, RG59 and RG6/6Q; RG7 and RG11 with PA1175
- Cuts solid or stranded cable up to AWG 6
- Precise and effortless cuts
- Round cutting form won't deform cables













PA1902 Adapter RJ45 Modular 8-Way

- Nylon-reinforced ABS plastic body
- Easy-to-read wire layout
- Removable/replaceable patch cord
- Inline adapters
- Snagless plugs
- Belt clip
- Notched copper contacts keep alligator clips attached during testing

PA1923 Untwist Tool Twisted Pair

- Flares RG59, RG6 and RG6 Quad Cable types
- · Works with CATV "F" connectors
- · Save time on cable TV and satellite installations
- Flare the shield braid back from the dielectric without nicking your finger
- Make connections faster and easier with properly prepped cable
- Attachment tool enables you to hold the connector comfortably to insert onto cable

PA4574 Blade Surepunch BIX

- Increased HI/LO impact force to meet demands of new cable types and AWG sizes:
 LO= 30 lbs (133 N), HI= 40 lbs (178 N)
- For 28-22 AWG (0.08 0.34mm2), solid or stranded wire
- Cushion grip, molded to the shape of your hand, for comfort and a sure, non-slip hold
- Uses twist-and-lock style blades
- · Cushioned heel for comfort in the palm of your hand
- New latch cover blade storage area in end of handle
- · Lanyard holes in end

PA9546 CONN RJ45 8P8C CAT-5e Bulk

- Increased HI/LO impact force to meet demands of new cable types and AWG sizes:
 LO= 30 lbs (133 N), HI= 40 lbs (178 N)
- For 28-22 AWG (0.08 0.34mm2), solid or stranded wire
- Cushion grip, molded to the shape of your hand, for comfort and a sure, non-slip hold
- Uses twist-and-lock style blades
- Cushioned heel for comfort in the palm of your hand
- New latch cover blade storage area in end of handle
- · Lanyard holes in end

PA3590 Surepunch-Pro Sub-Assembly w/Labels

- Terminate cable in single punch including 23 AWG Cat6
- Adjustable HI/LO spring compression for all cable types. LO= 27.5 lbs (122 N), HI= 37.5 lbs (167 N)
- Detachable light with long-life LED specially designed to focus the light on the panel work area
- Luminous intensity of the LED is 2200 mcd
- Finger grips and non-slip rubber-embedded cushioned handle for comfort
- Multi-use spudger that can be used as a screwdriver or an IDC contact insertion tool
- · Hook to feed wires through holes
- Pick to separate bonded twisted-pair cables or to strip insulation and cut wire
- Uses twist-and-lock style blades
- Blade storage area in end of handle with comfortable latch cover

PA1927 3-Way CATV Prep Tool Black Bulk Pkg

- Flares RG59, RG6 and RG6 Quad Cable types
- Works with CATV "F" connectors
- Save time on cable TV and satellite installations
- · Flare the shield braid back from the dielectric without nicking your finger
- Make connections faster and easier with properly prepped cable
- Attachment tool enables you to hold the connector comfortably to insert onto cable

PA4591 PDT Blade Double 110

- For 28-22 AWG (0.08 0.34mm2), solid or stranded wire
- Cushion grip, molded to the shape of your hand, for comfort and a sure, non-slip hold
- Increased HI/LO impact force to meet demands of new cable types and AWG sizes: LO= 30 lbs (133 N), HI= 40 lbs (178 N)
- Uses twist-and-lock style blades
- · Cushioned heel for comfort in the palm of your hand
- New latch cover blade storage area in end of handle
- · Lanyard holes in end

PA4575 Blade Surepunch Krone LSA

- For 28-22 AWG (0.08 0.34mm2), solid or stranded wire
- Cushion grip, molded to the shape of your hand, for comfort and a sure, non-slip hold
- Increased HI/LO impact force to meet demands of new cable types and AWG sizes:
 LO= 30 lbs (133 N), HI= 40 lbs (178 N)
- · Uses twist-and-lock style blades
- Cushioned heel for comfort in the palm of your hand
- New latch cover blade storage area in end of handle
- · Lanyard holes in end

PA9520 CONN RJ11 6P6C Bulk

- RJ11 6-conductor modular plugs
- 50 micron gold plating
- For use with stranded wire

PA4573 Blade Surepunch 66 Twist-Lock Blade RM

- For 28-22 AWG (0.08 0.34mm2), solid or stranded wire
- Cushion grip, molded to the shape of your hand, for comfort and a sure, non-slip hold
- Increased HI/LO impact force to meet demands of new cable types and AWG sizes:
 LO= 30 lbs (133 N), HI= 40 lbs (178 N)
- Uses twist-and-lock style blades
- · Cushioned heel for comfort in the palm of your hand
- New latch cover blade storage area in end of handle
- Lanuard holes in end

PA9641 CONN RG6 RG6Q H20 Compression

PA9523 CONN Handset 4P4C Flat Stranded

PA427626 CST LC-CST RG6 Pre-Set Coax Stripper

PA4578 Blade Surepunch 110 Round

1390 Aspen Way Vista, CA • 92081

TC-PA4932 02/21

Latin America Phone : 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927050 ©2021 Tempo Communications Inc. • An ISO 9001 Company

EMEA Office: Tempo Europe Limited

Brecon House, William Brown Close, Cwmbran • NP44 3AB, UK

TempoCom.com | tel 800.642.2155 | sales@tempocom.com



Renewed Vision. **Innovation** Forward.











