

FLOOR CARE STRIPPER

ANIMAL™

Powerful Rinse-Free Stripper

- A fiercely aggressive, fast-working, and rinse-free floor stripper
- Removes polyurethane and water-based finishes and sealers including, metal interlocks
- Non-ammoniated, phosphate-free, biodegradable formula

This product is designed for the effective removal of heavy wax build-up in a single pass. Quickly removes tough urethane-fortified floor finishes and water-based sealers (including metal interlocks). Leaves floors ready for re-application of new floor finish. Minimal contact time and rinse-free concentrated formula reduce labor and overall cost.

DIRECTIONS FOR USE:

Mix product thoroughly before use. Always test in an inconspicuous area before application. Restrict pedestrian traffic when this product is in use. This product can be mixed with hot or cold water. Optimum dilution will depend on floor conditions.

Spread stripping solution liberally over floor and let stand for 10-20 minutes. Do not allow solution to dry on floor. Scrub thoroughly with a floor machine to break up the softened film. Pick up dirty solution with a wet vac or auto-scrubber. No need for rinsing. Detail mop the floor to remove all residues and let clean floor dry completely before refinishing with a floor finish.

RECOMMENDED DILUTIONS:

Remove 1-2 coats:	Dilute 1:12	11 oz. per gallon of water
Remove 2-4 coats:	Dilute 1:8	16 oz. per gallon of water
Remove Multiple Coats:	Dilute 1:4	32 oz. per gallon of water

IMPORTANT SAFETY INFORMATION:



DANGER

Harmful in contact with skin. Causes severe skin burns and eye damage. May cause respiratory irritation.

PRECAUTIONS:

Do not breathe vapors. Wash hands thoroughly after handling. Use only outdoors or in a well-ventilated area. Wear protective gloves, protective clothing, eye protection and face protection. Store in a well-ventilated place. Keep container tightly closed. Store locked up. Dispose of contents and container in accordance with local, regional, national and international regulations.

FIRST AID:

IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. Immediately call a POISON CENTER or physician.

IF ON SKIN (or hair): Remove immediately all contaminated clothing. Rinse skin with water. Wash contaminated clothing before reuse.

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

CONTAINS:

2-butoxyethanol 111-76-2, 2-aminoethanol 141-43-5, sodium hydroxide 1310-73-2, alcohols, C9-11, ethoxylated 68439-46-3.



APPLICATIONS

- Nursing homes
- Schools
- Hospitals
- Health care applications


SPECIFICATIONS

Color	Colorless
Fragrance	Solvent-like
pH Range	12.0 - 14.0
Form	Liquid
Dilution Range	11 oz. - 32 oz. per gallon

PACKAGING

4/1 Gallon	100455-505840
5 Gallon Pail	100455-505841
55 Gallon Drum	100445-505846

PROP 65 INFO

 **WARNING:** This product can expose you to chemicals including 2,2'-iminodiethanol (111-42-2) which is known to the State of California to cause Cancer. For more information go to www.P65Warnings.ca.gov.



Contact your Account Representative for more information

7373 Rowlett Park Dr., Tampa, FL 33610 | 813.237.6463 | Emergency #800.255.3924 | theochem.com

©2022 Theochem Laboratories Inc. All right reserved. | Made in the USA