

FLOOR CARE

NEUTRAL CLEANER

LACTO TOP SCRUB

Concentrated Top Scrub

- Designed for interim floor finish maintenance
- Removes the top layer of floor finish, preparing the surface for re-coating
- High-performance general cleaner for numerous surfaces

This product is the first step in the top scrub and re-coat procedure. The top scrub (and re-coating) extend the time between stripping and refinishing, reducing maintenance and labor costs. This product may also be used (when diluted as directed) to clean tile and marble, leather and plastic, automobile surfaces, woodwork, painted surfaces, and more.

DIRECTIONS FOR USE:

TOP SCRUBBING WAXED AND FINISHED FLOORS: Dilute 3 oz. per gallon of water. Use a mop or automatic scrubber to agitate the solution using a green cleaning pad or brush. Remove the dirty solution from the floor with a mop, wet vacuum, or automatic scrubber. When removed properly, no flood rinsing is required. After the floor has dried, check for residue. If any residue is present, a rinse will be needed.

TERRAZZO, TILE, AND MARBLE: Dilute 3 oz. per gallon of water. The mop floor then rinses with clear water. In extremely dirty conditions, use a stronger solution with hot water.

LINOLEUM, ASPHALT, AND VINYL FLOORS: Dilute 3 oz. per gallon of water. The mop floor then rinses with clear water.

WAX REMOVING: Dilute 10 oz. per gallon of warm water. Apply to the floor, let sit for 10 minutes. Scrub with stripping pad, then rinse with clear water.

LEATHER AND PLASTIC: Dilute 2 oz. per gallon of water. Spread thinly over the surface then wipe dissolved dirt off with a clean damp cloth or sponge. Rinse with clear water.

AUTOMOBILES AND TRUCKS: Dilute 2 oz. per gallon of water. Apply with a sponge or brush, then rinse with clear water.

WOODWORK, PAINTED SURFACES, ETC.: Dilute 2 oz. per gallon of water. Apply with a sponge then, wipe off with a damp cloth. Rinse with clear water. Wipe dry with a clean, dry cloth.

GENERAL FLOOR CLEANING: Dilute 1/4 oz. per gallon of water. Mop the floor, then rinse with clear water.

DAIRIES, FOOD PROCESSORS, AND MEAT PACKING PLANTS: Dilute 2 oz. per gallon of warm water. Use as a general cleaning agent on all surfaces. This product can be used with steam or mechanical cleaning devices. Before using this compound, food must be carefully protected or removed. After using, rinse all surfaces with potable water.

IMPORTANT SAFETY INFORMATION:



DANGER

Causes skin irritation. Causes serious eye damage.

PRECAUTIONS:

Wear protective gloves, protective clothing, eye protection and face protection. Wash hands thoroughly after handling. Dispose of contents and container in accordance with local, regional, national and international regulations.

FIRST AID:

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or physician.

IF ON SKIN: Wash with plenty of water. If skin irritation occurs: Get medical attention. Take off contaminated clothing and wash before reuse.

CONTAINS:

Sodium dodecylbenzenesulphonate (25155-30-0), sodium xylenesulphonate (1300-72-7), Coconut diethanolamide (68603-42-9), sodium hydroxide (1310-73-2), diethanolamine (111-42-2).



APPLICATIONS

- Kitchens
- Restaurants
- Bathrooms

SPECIFICATIONS

Color	Pink
Fragrance	Citrus
pH Range	9.0 - 9.8
Form	Liquid
Dilution Range	1/4 oz. - 10 oz.

PACKAGING

4/1 Gallon	100483-500389
5 Gallon Pail	100483-500387
55 Gallon Drum	100483-505359

PROP 65 INFO

WARNING: This product can expose you to chemicals including Coconut diethanolamide, which is known to the State of California to cause Cancer. For more information go to www.P65Warnings.ca.gov.