

FLOOR CARE

NEUTRAL CLEANER

RINSE NO MORE PLUS LAVENDER

Concentrated, Neutral Floor & All Purpose Cleaner

- Cleans and leaves a long-lasting fresh lavender scent
- Leaves no residue, no need to rinse
- For use on floors and virtually all hard surfaces

This product is a non-alkaline (non-acid) formula for picking up the soil and never needs rinsing. Will not bite, blush, haze, or dull the shine, as can high alkaline all-purpose cleaners. Fresh, long-lasting lavender fragrance. For use on floors and virtually all hard surfaces.

DIRECTIONS FOR USE:

Automatic Scrubber:

Use a light cleaning pad. Vacuum up. No rinse needed.
Dilute 1:64 2 oz. per gallon of cool water.
Dilute 1:64 30 oz. per 15 gallons of cool water in a tank.

Ultra High Speed Floor Care:

Always clean with this product before burnishing.
Once it is dry, your clean floor is ready for high speed burnishing.

Heavy Floor Cleaning:

Dilute 1:21 6 oz. per gallon of cool water.

Damp Mop:

Damp mop floors. Let dry. No rinse needed.
Dilute 1:40 3 oz. per gallon of cool water in a bucket.

All-Purpose Cleaning of Floors:

Mop floor surface with the solution. Let dry, no-rinse needed.
Dilute 1:64 2 oz. per gallon of cool water in a bucket.

Bathrooms and Walls:

Use the product on a wet sponge; clean surfaces.

Counters, Sinks and Vanities:

Use the product on a wet sponge; clean surfaces. Always rinse food contact surfaces thoroughly after cleaning with this product.

IMPORTANT SAFETY INFORMATION:

PRECAUTIONS:

Wear protective gloves, protective clothing, eye protection and face protection. Wash hands thoroughly after handling

FIRST AID:

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention.

CONTAINS: Alcohols, C9-11, ethoxylated (CAS:# 68439-46-3) and 1-propoxypropan-2-ol (CAS: 1569-01-3).



APPLICATIONS

- Kitchens
- Restaurants
- Bathrooms

SPECIFICATIONS

Color Violet
Fragrance Pleasant
pH Range 6.5 - 8.5
Form Liquid
Dilution Range Depends on application

PACKAGING

4/1 Gallon 100447-500261
5 Gallon Pail 100447-500258
55 Gallon Drum 100447-500260

PROP 65 INFO

n/a



Contact your Account Representative for more information

7373 Rowlett Park Dr., Tampa, FL 33610 | 813.237.6463 | Emergency #800.255.3924 | theochem.com

©2022 Theochem Laboratories Inc. All right reserved. | Made in the USA