

19 577

LINEARE™

4-HOLE SINGLE-HANDLE DECK MOUNT ROMAN TUB FAUCET WITH 1.75 GPM HAND SHOWER

*Pure Freude
an Wasser*



STANDARD SPECIFICATION:


- GROHE StarLight®
- 8 3/8" Spout reach
- 4 1/8" Aerator height
- Sena Stick hand shower (28 034), 1.75gpm
- 79" Metal hose
- Pre-assembled spout fixing
- OHM operating element
- Metal lever
- Bath inlet with mousseur
- Diverter bath/shower
- Flexible connection hoses
- Connection for shower hose
- Protected against backflow



PRODUCT FEATURES:

-  **GROHE StarLight®**
-  **GROHE SilkMove®**

CERTIFICATIONS:

-  **CEC**
- CEC Certified
- CALGreen Compliant
- Massachusetts Plumbing Board Approved
- Energy Policy Act of 1992
- CSA B125.1
- ASME A112.18.1

AVAILABLE FINISHES:

- 19577001**  GROHE StarLight® Chrome
- 19577A01**  Hard Graphite
- 19577EN1**  Brushed Nickel InfinityFinish™
- 19577GN1**  Brushed Cool Sunrise

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 07-06-2022

US
Tel: 1.630.582.7711 Fax: 1.630.582.7722
For the most current Specification Sheet,
go to www.grohe.us.

Canada
Tel: 1.888.644.7643 Fax: 1.905.366.2071
For the most current Specification Sheet,
go to www.grohe.ca.

PART OF LIXIL

19 577

LINEARE™

*Pure Freude
an Wasser*



4-HOLE SINGLE-HANDLE DECK MOUNT
ROMAN TUB FAUCET WITH 1.75 GPM
HAND SHOWER

TECHNICAL DATA:

Product Height	9-5/8 in
Product Width	21-3/4 in
Fitting Spout Height	4-1/8 in
Fitting Spout Reach	8-3/8 in
GPM (Min)-GPM (Max)	1.75 gal (US)/min

