

24 111

**GROHTHERM®**

## DUAL FUNCTION 2-HANDLE THERMOSTATIC VALVE TRIM WITH CONTROL MODULE

*Pure Freude  
an Wasser*



### STANDARD SPECIFICATION:

- GROHE StarLight®
- GROHE TurboStat® compact cartridge with wax thermoelement
- Thermostatic temperature control with GROHE SafeStop safety button at 100°F/38°C
- GROHE SafeStop Plus temperature limiter at 115° F/46° C
- 6 1/4" Metal wall trim plate with GROHE QuickFix® (concealed mounting screws)
- Metal trim angle adjustable up to 6°
- GROHE AquaDimmer (top handle) includes integrated shut off & 2-way diverter (2 discrete functions)
- ADA compliant lever handles
- Includes service stops
- 7.1gpm at 45psi
- Optional AquaDimmer stop ring for shared function (14 060 000) (sold separately)
- Requires GROHE Rapido® SmartBox (35 601 000) (sold separately)



### PRODUCT FEATURES:

-  **GROHE StarLight®**
-  **GROHE QuickFix®**
-  **GROHE TurboStat®**

### CERTIFICATIONS:



- CEC Certified
- Massachusetts Plumbing Board Approved
- N/A
- ASSE 1016
- CSA B125.1
- CSA B125.16
- ASME A112.18.1
- ASME A112.1016

### AVAILABLE FINISHES:

- 24111000**  GROHE StarLight® Chrome
- 24111A00**  Hard Graphite
- 24111E00**  Brushed Nickel InfinityFinish™
- 24111G00**  Brushed Cool Sunrise

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 07-06-2022

**US**  
Tel: 1.630.582.7711 Fax: 1.630.582.7722  
For the most current Specification Sheet,  
go to [www.grohe.us](http://www.grohe.us).

**Canada**  
Tel: 1.888.644.7643 Fax: 1.905.366.2071  
For the most current Specification Sheet,  
go to [www.grohe.ca](http://www.grohe.ca).

PART OF **LIXIL**

24 111

**GROHTHERM®**

DUAL FUNCTION 2-HANDLE  
THERMOSTATIC VALVE TRIM WITH  
CONTROL MODULE

*Pure Freude  
an Wasser*



**TECHNICAL DATA:**

Product Height	6-1/4 in
Product Length	1-11/16 in
Product Width	6-1/4 in

