

30 377

DEFINED™

SINGLE-HANDLE PULL DOWN KITCHEN FAUCET DUAL SPRAY 1.75 GPM

Pure Freude
an Wasser






STANDARD SPECIFICATION:

- GROHE SilkMove®
- GROHE StarLight®
- Pull-down dual spray with toggle function: switches between regular water flow and spray without turning off the water
- 15 9/16" Faucet height
- 8 7/8" Aerator height
- 8 11/16" Faucet reach
- SpeedClean® anti-lime system
- Forward rotation lever - does not hit backsplash
- 360° Swivel radius
- Solid brass body
- Flexible connection hoses
- 1.75gpm flow rate
- CALGreen compliant



PRODUCT FEATURES:

-  GROHE SilkMove®
-  GROHE StarLight®
-  Speed Clean®

CERTIFICATIONS:



- ADA
- CEC Certified
- Low Lead Certified
- CALGreen Compliant
- Massachusetts Plumbing Board Approved
- Energy Policy Act of 1992
- NSF 372
- CSA B125.1
- ASME A112.18.1
- Complies with lead plumbing laws

AVAILABLE FINISHES:

30377000



GROHE StarLight®
Chrome

30377DC0



SuperSteel
InfinityFinish™

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

Tel: 1.630.582.7711 Fax: 1.630.582.7722

We reserve the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.grohe.us.

06-21-2021

PART OF **LIXIL**

30 377

DEFINED™

SINGLE-HANDLE PULL DOWN KITCHEN
FAUCET DUAL SPRAY 1.75 GPM

*Pure Freude
an Wasser*



TECHNICAL DATA:

Product Height	14-9/16 in
Product Width	5-1/16 in
Fitting Spout Height	8-7/8 in
Fitting Spout Reach	8-11/16 in
GPM (Min)-GPM (Max)	1.75 gal (US)/min

