

26 870

RAINSHOWER™

20" CEILING SHOWER HEAD 1
SPRAY, 1.75 GPM



GROHE SPA

STANDARD SPECIFICATION:

- GROHE StarLight®
- GROHE DreamSpray®
- GROHE EcoJoy®
- Speed Clean® anti-lime system
- 20" x 20"
- Flush mount
- 1 Spray: Rain
- Metal shower head
- 252 Spray nozzles
- ½" NPT female threads
- Max. flow rate: 1.75gpm (6.6L/min)



PRODUCT FEATURES:

-  GROHE StarLight®
-  GROHE DreamSpray®
-  GROHE EcoJoy™
-  Speed Clean®

CERTIFICATIONS:



- WaterSense
- CEC Certified
- CALGreen Compliant
- Massachusetts Plumbing Board Approved
- Energy Policy Act of 1992
- CSA B125.1
- ASME A112.18.1

AVAILABLE FINISHES:

26870000  GROHE StarLight® Chrome

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 04-26-2023

US
Tel: 1.630.582.7711 Fax: 1.630.582.7722
For the most current Specification Sheet,
go to www.grohe.us.

Canada
Tel: 1.888.644.7643 Fax: 1.905.366.2071
For the most current Specification Sheet,
go to www.grohe.ca.

PART OF **LIXIL**

26 870

RAINSHOWER™

20" CEILING SHOWER HEAD 1
SPRAY, 1.75 GPM



GROHE SPA

TECHNICAL DATA:

Product Height	1/2 in
Product Length	20 in
Product Width	20 in
GPM (Min)-GPM (Max)	1.75 GPM

