

### DESCRIPTION

- Metal construction with various finishes identified by suffix
- Includes optional 3 hole deck plate (escutcheon)
- Flexible supplies with 3/8" compression fittings

### OPERATION

- Pivot action lever style handle
- Temperature controlled by 100° arc of handle travel

### FLOW

 Water usage is limited to these maximum flow rates as indicated by the corresponding product markings
 ° 1.2 gpm max (4.5L/min) at 60 psi

### CARTRIDGE

• 1255<sup>™</sup> Duralast<sup>™</sup> cartridge for Single-Handle Faucets


### STANDARDS

- Third party certified to WaterSense,<sup>®</sup> ASME A112.18.1/CSA B125.1, and all applicable requirements referenced therein
- Certified to NSF 61/9 & 372
- Products marked with 1.2 gpm are compliant with California water efficiency regulations
- Complies with California Proposition 65 and with the Federal Safe
  Drinking Water Act
- ADA 🚯 for lever handle

### WARRANTY

- Lifetime limited warranty against leaks, drips and finish defects to the original homeowner
- 10 year limited warranty when used in a multifamily installation
- 5 year limited warranty when used in a commercial installation Visit www.moen.com/support for complete details and limitations

# Specifications




## TILSON<sup>™</sup> Single Handle Lavatory Faucet

### Models: 84565 series

### **NOTE:** THIS FAUCET IS DESIGNED TO BE INSTALLED THROUGH 1 HOLE, 1-1/8" MIN. DIA.





#### 

6603800005

SPC19915

M/14/2029