MOEN[®]

DESCRIPTION

· Metal construction with various finishes identified by suffix

OPERATION

- · Lever style handle
- Hot side counterclockwise to open (clockwise to close), cold side clockwise to open (counter-clockwise to close)
- Will operate with less than 5 lbs. of force

FLOW

• Aerator is limited to 1.5 gpm max (5.7 L/min)

CARTRIDGE

- 1224 cartridge design
- Engineered polymers, non-ferrous and stainless steel materials


STANDARDS

- Third party certified to ASME A112.18.1/CSA B-125.1 and all applicable requirements referenced therein
- Certified to NSF 61/9 & 372
- Meets CalGreen and Georgia SB370 requirements
- Complies with California Proposition 65 and with the Federal Safe Drinking Water Act
- ADA for lever handles

WARRANTY

- Lifetime limited warranty against leaks, drips and finish defects to the original homeowner
- 10 year limited warranty when used in a multifamily installation
- 5 year limited warranty when used in a commercial installation Visit www.moen.com/support for complete details and limitations


Specifications



Caldwell™ Two-Handle High Arc Spout Lever Style Kitchen Faucet

Models: 87859 series

NOTE: This faucet is designed to be installed through 3 holes 1" Min. Dia.



CRITICAL DIMENSIONS

(DO NOT SCALE)