

Open Towel / Tissue Holder Installation Instructions

**Model No. 10-27, 12-27, 13-27, 15-27, 16-27, 17-27, 19-27, 22-27, 23-27, 24-27,
26-27, 30-27, 31-27, 33-27**

Recommended Installation by a Professional Contractor

1. Drill hole in wall at desired location using the appropriate drill size:

- Wood Screw (#6 x 2") - use: 3/32" Drill
- Toggle Screw (6-32 x 3") - use: 3/8" Drill

2. Fasten FLANGE (1) to wall using either WOOD/TOGGLE SCREWS (2). (See Fig. 1)

(Model 26-13, with Square BASE (1) configuration, (not shown) to be level.)

3. Position SPLINE (4), per the Table below, at the proper height from mounting surface. Secure into place by tightening SETSCREW (5). (See Fig. 2)

MODEL	10-, 15-	23-	13-, 16-	24-, 26-, 33-	17-, 22-	29-	30-, 31-
POST HT.	2 5/16"	2-9/16"	2-1/8"	2-1/16"	2-3/16"		

4. Temporarily place END POST (6) onto FLANGE (1) to check alignment. If necessary, loosen lower screw on FLANGE (1) and adjust. Retighten screw.

5. When applicable to model, locate the ESCUTCHEON and or DECORATIVE RING (7) over FLANGE (1), otherwise - Place END POST (6) over SPLINE (4) and against the ESCUTCHEON (7) or FLANGE (1). Secure into place by tightening the SETSCREW (5). (See Fig. 3)

5a. When applicable to model, insert the ESCUTCHEON NUT (8) into top of ESCUTCHEON (7). (See Fig. 3a) Assemble and secure with additional items per Fig. 3.

5b. In addition to an ESCUTCHEON NUT (8), CRYSTAL ESCUTCHEON (7) also contains an ESCUTCHEON SHROUD (9). (See Fig. 3b) Assemble and secure with additional items per Fig. 3.

