

STANDARD CHECK VALVES

Liberty Pumps®

A Family and Employee Owned Company

Economy Check Valves



CV2N1 1-1/4" and 1-1/2" combo

CV150 1-1/2"

CV200 2"

- ABS valve body
- Rubber slip connect with hose clamps
- Vertical or horizontal installation
- 15 PSI rated at 104°F for CV2N1 and CV150
- 25 PSI rated at 140°F for CV200

Thread X Barb Fit



CV150-125T 1-1/2" MPT x 1-1/4" Barb

CV150-150T 1-1/2" MPT x 1-1/2" Barb

- PVC construction
- Thread directly into 1-1/2" sump pump discharge
- 30 PSI rated at 104°F

Cast Iron High-temperature 200°F



HCV150 1-1/2"

HCV200 2"

- Heavy-duty cast iron body
- Full flow
- High-temperature rubber flapper - 200°F
- 125 PSI rated
- Vertical or horizontal installation
- Female NPT connections

Ball/Check/Union Combination



BCV150 1-1/2"

BCV200 2"

- Ball/check combo provides compact design
- Heavy-duty PVC
- 150 PSI rated at 72°F
- 30 PSI rated at 140°F
- Vertical or horizontal installation
- Features union for easy disassembly
- Socket weld connections

Heavy-Duty Compression Fit



CV2N1C 1-1/4" and 1-1/2" combo

CV200C 2"

CV300C 3"



- Heavy-duty PVC
- Vertical or horizontal installation
- 150 PSI rated at 72°F for CV2N1C and CV200C
- 30 PSI rated at 140°F for CV2N1C and CV200C
- 125 PSI rated at 72°F for CV300C
- 25 PSI rated at 140°F for CV300C