

U.S. Government

Federal law prohibits removal of this label before consumer purchase.

# ENERGYGUIDE

Instantaneous Water Heater -Natural Gas  
Capacity (max. flow rate):4.7 gpm

RINNAI  
Model REU-VC2837WD-US



## Estimated Yearly Energy Cost

**\$230**



\$195.0

\$230.0

Cost Range of Similar Models

## Maximum Gallons Per Minute of Hot Water (GPM Rating)

very small	low	medium	<b>high</b> 4.7 gpm
------------	-----	--------	------------------------

- Your cost will depend on your utility rates and use.
- Cost range based only on models fueled by Natural Gas with a high maximum gallons per minute of hot water (greater than 4 gpm).
- Estimated energy cost based on a national average Natural Gas cost of \$1.09 per therms
- Estimated yearly energy use: 209 therms.