

U.S. Government

Federal law prohibits removal of this label before consumer purchase.

ENERGYGUIDE

Instantaneous Water Heater - Natural Gas
Capacity (max. flow rate): 4.9 gpm

RINNAI
Model REU-VC2837FFUD-US



Estimated Yearly Energy Cost

\$230

\$195.0

\$230.0

Cost Range of Similar Models

Maximum Gallons Per Minute of Hot Water (GPM Rating)

very small	low	medium	high 4.9 gpm
------------	-----	--------	------------------------

- Your cost will depend on your utility rates and use.
- Cost range based only on models fueled by Natural Gas with a high maximum gallons per minute of hot water (greater than 4 gpm).
- Estimated energy cost based on a national average Natural Gas cost of \$1.09 per therms
- Estimated yearly energy use: 209 therms.