KOHLER, Faucets

Statement[™] VES

Single-function handshower, 1.5 gpm K-20998

Features

- Wide coverage spray produces an encompassing spray for everyday use.
- 1.5 gpm (5.7 lpm) maximum flow rate handshower allows you to save water without sacrificing performance or coverage.
- Variable-flow lever lets you adjust from 1.5 gpm (5.7) lpm) down to 0.5 gpm (1.9 lpm) water pause for greater conservation during your shower routine.
- Soft silicone sprayface is easy to clean.
- Magnetic docking securely holds the handshower in place when paired with the Statement VES handshower holder and supply elbow.

Material

KOHLER finishes resist corrosion and tarnishing.

Technology

 Katalyst[®] air-induction technology infuses water with air, creating bigger drops for a more powerful spray.

Installation

- Bracket or slidebar required for wall-mount installation.
- Deck-mount holder required for deck-mount installation.

Water Conservation & Rebates

This product can help a building earn Water Efficiency points in LEED® Green Building Rating System.

Recommended Products/Accessories

K-21051 Wall-mount handshower holder and supply elbow K-21049 60" shower hose K-21050 72" shower hose K-23723 Faucet cleaner







Codes/Standards ASME A112.18.1/CSA B125.1 DOE - Energy Policy Act 1992 EPA WaterSense® California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 OBC

KOHLER® Faucet Lifetime Limited Warrantv

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description


- CP **Polished Chrome**
- Vibrant® Brushed Nickel BN
- BL Matte Black




KOHLER, Faucets

Statement[™] VES

Single-function handshower, 1.5 gpm K-20998





Technical Information

All product dimensions are nominal.

Handshower:

Rated maximum
flow:1.5 gal/min (5.7 l/min)Pressure:45 psi (3.1 bar)

Notes

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

