

Occasion[™] Single-handle bathroom sink faucet, 1.0 gpm

K-27000-4K

Features

- A single handle controls both on/off activation and temperature setting
- 5-5/16" (135 mm) spout reach
- 1.0 gpm (3.8 lpm) maximum flow rate at 60 psi (4.14 bar)
- KOHLER ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Metal pop-up drain with lift rod and tailpiece
- Part of the Occasion bathroom faucet and accessory collection

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Single hole
- Preattached flexible supply lines simplify installation







Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61 NSF/ANSI/CAN 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 EPA WaterSense™ California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 OBC

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color Code Description

SN	Vibrant [™] Polished Nickel
BV	Vibrant [™] Brushed Bronze
BL	Matte Black
2MB	Vibrant™ Brushed Moderne
	Brass Matte Black with Moderne
	BV BL



KOHLER, Faucets

Occasion[™] Single-handle bathroom sink faucet, 1.0 gpm K-27000-4K



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate:1 gal/min (3.8 l/min)Pressure:60 psi (4.1 bar)Drain included:YesDrain with overflow:YesSpout:5-5/16" (135 mm)

Notes

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

