

KOHLER® Faucets

Two-handle utility sink faucet with 3/4" threaded spout

Jolt™
K-30619

Features

- Threaded swing spout with 7" (178 mm) reach
- 3/4" (19 mm) GHT at faucet outlet for attaching garden hose or other accessory
- Two lever handles offer separate control of hot and cold water
- 4.0 gpm (15.1 lpm) minimum flow rate at 20 psi (1.3 bar)
- Quarter-turn washerless ceramic disc valves
- Less drain

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- For 4" (102 mm) centers
- Three-hole installation

Recommended Products/Accessories

K-23723 Faucet cleaner

Optional Products/Accessories

1012715



Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

All applicable US Federal and State material regulations

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

