

### Features

- Two full-extension 12-3/4" (325 mm) drawers with soft-close side-mount slides
- Three-way adjustable slow-close door hinges for easy cabinet access
- 18" (457 mm) cabinet interior provides ample storage space
- Finish-matched cabinet interior offers generous clearance for plumbing
- Customize your storage with optional accessories such as floor liners, drawer organizers, and perfectly sized containers (sold separately)
- Coordinates with K-33534 upgraded hardware finishes, K-25816 quartz backsplash, and K-25819 quartz side splash (sold separately)

### Material

- Quartz vanity top adds beauty and long-lasting durability
- Solid wood and moisture-resistant MDF
- Painted exterior

### Installation

- Easy installation – no special tools required
- Separate vanity top makes for simplified installation



### Codes/Standards

ASME A112.19.2/CSA B45.1  
EPA TSCA Title VI/CARB P2



### KOHLER® One-Year Limited Warranty



See website for detailed warranty information.

### Available Colors/Finishes


*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
	1WX	Grey Slate



**Waste Pipe Location Information**



### Technical Information

All product dimensions are nominal.

### Notes

Install this product according to the installation instructions.