



# Rite-Temp® 1.75 gpm bath and shower trim K-TS395-4G

### **Features**

- Pressure-balancing diaphragm technology maintains outlet temperature within +/-3°F during water pressure fluctuations.
- Antiscald protection.
- A single handle controls both on/off activation and temperature setting.
- Includes faceplate with ADA-compliant metal level handle.
- Includes diverter bath spout with 1/2" NPT connection.
- Single-function 1.75 gpm (6.6 lpm) showerhead with Katalyst® air-induction technology.
- MasterClean<sup>™</sup> sprayface features an easy-to-clean surface that withstands mineral buildup.
- Coordinates with Devonshire faucets, accessories, and showering components to complete your bathroom.

### Material

- Premium material construction with metal handle ensures reliability and durability.
- KOHLER finishes resist corrosion and tarnishing.

### Installation

 Trim only; requires valve to complete installation (sold separately).

# **Required Products/Accessories**

K-304 Series Rite-Temp® Valves

or

K-8304 Series Rite-Temp® Valve & Cartridge Kits

or

K-8300 Series Rite-Temp® Valve Body Rough-ins K-8305 Series Rite-Temp® Cartridges

or

K-2971-KS 3/4" Pressure-balancing Valve

# Adapters, Rough-in and Extension Kits

GP1030932 Range: 3-1/2" (89 mm) - 4-1/4" (108 mm)

### **Optional Products/Accessories**

K-10350 Deep rough-in kit K-10351 Test cap for K-8300 Series valve bodies 88526 Thin Wall Trim Kit









## Codes/Standards

ASME A112.18.1/CSA B125.1 DOE - Energy Policy Act 1992 EPA WaterSense® California Energy Commission (CEC)

# **KOHLER® Faucet Lifetime Limited**Warranty

See website for detailed warranty information.

### **Available Colors/Finishes**

Color tiles intended for reference only.


| Color | Code | Description             |
|-------|------|-------------------------|
|       | CP   | Polished Chrome         |
|       | PB   | Vibrant® Polished Brass |
|       | BN   | Vibrant® Brushed Nickel |
|       | 2BZ  | Oil-Rubbed Bronze       |





# **Devonshire®**

# Rite-Temp® 1.75 gpm bath and shower trim **K-TS395-4G**



### **Technical Information**

All product dimensions are nominal.

Drain included: No

### Showerhead/Body Spray:

Rated maximum 1.75 gal/min (6.6 l/min)

flow:

Pressure: 80 psi (5.5 bar)

## **Notes**

For use with automatic compensating valves rated at 1.4 gal/min (5.3 l/min) or less.

Install this product according to the installation instructions.

Install straight pipe or tube drop of 7" (178 mm) to 18" (457 mm) with single elbow between the valve and the wall-mount spout.

NOTICE: Risk of product damage. Long screws, for installing trim, can damage the K-2971-KS valve. Consult the trim installation guide to verify if the thin wall installation kit is needed.

