



HAND SHOWER

- 2-Spray Setting Hand Shower
- Touch-Clean® Nozzles

STANDARD SPECIFICATIONS:

- Max flow rate 1.5 gpm @ 80 psi, 5.7 L/min @ 550 kPa
- Certified dual check valves for backflow protection
- Change spray modes with pushbutton
- Hand held shower with two spray settings - pause is a non-positive shut-off
- 60" (1524 mm) Ultra Flex hose
- Wall mount bracket for hands-free showering
 - P60210 only
- 27" (687 mm) wall bar with adjustable slide
 - P62410 only

WARRANTY

- Parts and Finish - Lifetime limited warranty; or for commercial purchasers, 10 years for multi-family residential (apartments and condominiums) and 5 years for all other commercial uses, in each case from the date of purchase.



▲ Designate Proper Finish Suffix

Spray Pattern



Full Body Spray



Pause

COMPLIES WITH

- ASME A112.18.1 / CSA B125.1
- Indicates compliance to ICC/ANSI A117.1
- EPA WaterSense®