

26 866

SENA

STICK HAND SHOWER - 1 SPRAY



GROHE SPA

STANDARD SPECIFICATION:

- GROHE StarLight®
- GROHE DreamSpray®
- Speed Clean® anti-lime system
- 1 Spray: Non-adjustable wide spray
- Metal hand shower
- Inner WaterGuide for a longer life
- Max. flow rate: 2.5gpm (9.5L/min)
- Optional Adaptor Elbow (28 389) (sold separately)



PRODUCT FEATURES:

-  GROHE StarLight®
-  GROHE DreamSpray®
-  Speed Clean®

CERTIFICATIONS:



- WaterSense
- CEC Certified
- CALGreen Compliant
- Massachusetts Plumbing Board Approved
- Energy Policy Act of 1992
- CSA B125.1
- ASME A112.18.1

AVAILABLE FINISHES:

- 26866000  GROHE StarLight® Chrome
- 268662430  Matte Black
- 26866A00  Hard Graphite
- 26866EN0  Brushed Nickel InfinityFinish™
- 26866GN0  Brushed Cool Sunrise

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 04-26-2023

US
Tel: 1.630.582.7711 Fax: 1.630.582.7722
For the most current Specification Sheet,
go to www.grohe.us.

Canada
Tel: 1.888.644.7643 Fax: 1.905.366.2071
For the most current Specification Sheet,
go to www.grohe.ca.

PART OF LIXIL

26 866

SENA

STICK HAND SHOWER - 1 SPRAY



GROHE SPA

TECHNICAL DATA:

Product Height	215 mm
Product Length	32 mm
Product Width	32 mm
GPM (Min)-GPM (Max)	2.5 GPM

