29 424 LINEARE[™] PRESSURE BALANCE VALVE TRIM WITH 3-WAY DIVERTER WITH CARTRIDGE

STANDARD SPECIFICATION:

- All metal handles and trim plates to cater to the look and feel of a premium brand
- No visible screws for a clean uncluttered look
- GROHE QuickFix[®] fixation system provides a completely flush mounted trim with no wobble
- Easy to turn Lever Handles to meet all user needs
- Double Ceramic Cartridge for smooth, leak-free performance and improved scald protection
- Requires GrohSafe[™] 3.0 Pressure Balance Rough-in Valve with Integrated Diverter (35 117) (sold separately)



Pure Frende

an Wasser

PRODUCT FEATURES:

GROHE StarLight®

GROHE SilkMove®

GROHE QuickFix®

CERTIFICATIONS:

- CEC CEC
- ADA
- CEC Certified
- CALGreen Compliant
- Massachusetts Plumbing Board Approved
- ASSE 1016
- CSA B125.1
- CSA B125.16
- ASME A112.18.1
- ASME A112.1016

AVAILABLE FINISHES:



NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 01-20-2023

US Tel: 1.630.582.7711 Fax: 1.630.582.7722 For the most current Specification Sheet, go to www.grohe.us. Canada Tel: 1.888.644.7643 Fax: 1.905.366.2071 For the most current Specification Sheet, go to www.grohe.ca.



29 424 LINEARE[™] PRESSURE BALANCE VALVE TRIM WITH 3-WAY DIVERTER WITH CARTRIDGE

Pure Freude an Wasser



TECHNICAL DATA:

Product Height 242.10 mm

Product Length 59.80 mm

Product Width

196.80 mm

